

Recommended Start Formulation & Application Condition

White Gloss Enamel

PCR 927	360.00
Epoxy Resin (Razeen SR-5014	240.00
Ti O2 (Cristal 128)	192.50
Blanc Fix	192.50
Benzoin	5.00
Resinflow (Worlee PV 88)	10.00

Total **1000.00 Kg**

Application Condition

- **Extruder:** Twin screw with 500rpm and temp. at around 95 - 105 °C
- **Application:** 60 µm on 0.8 mm steel plate.
- **Curing:** 10 min. @ 200 °C

Film Properties

- **Gloss @ 60 (%)** 90
- **Direct Impact (kg/cm)** 160
- **Indirect Impact (kg/cm)** 160

The information and recommendations contained herein are based upon data believed to be correct. However, no guarantees or warranties are given for this technical advice. As a result, the application, the use and the processing of our products and the products manufacture by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. It is recommended that the consumers should evaluate the formulations in their own labs prior to production.